

Model T8 with single flex coupling type 966 for 0.2 to 20 Nm

nominal torque [Nm]	type 966; size	max. speed [U/min]	dimensions [mm]								MA [Nm]
			A	B	C	D	E	F	LA	P	
0.2	25	8000*	25.4	9	20,2	3...10	15	35	104.4	M4	1.4
0.5, 1	37	8000*	35.8	13.2	29.1	4...14	15	35	105.4	M4	1.4
2, 5	50	8000*	44.5	13.4	30.4	8...18	15	35	105	M5	3.1
10, 15	62	8000*	57.4	16.1	36.6	10...24	15	35	108.8	M5	6.1
20	62	6000*	57.4	16.1	36.6	10...24	20	40	148.8	M5	6.1

*increased number of revolutions on request

Please specify requested bore $\varnothing D$ at order.

