

**Model T2 / T4 / T6 with single flex coupling type 966 (clamping hub) for 0.03 to 30 Nm**

nominal torque [Nm]	type 966; size	max. speed [U/min]	dimensions [mm]						MA [Nm]
			A	B	D	F	LA	M	
0.03, 0.05	18	12000	19.1	7	3..7	15.6	68.2	2	0.4
0.1, 0.2	25	12000	25.4	9	3...10	20.2	89.4	2.5	0.8
0.5, 1	37	15000	35.8	13.2	4...14	29.1	88.8	3	1.4
2, 5	50	15000	44.5	13.4	8...18	30.4	91	4	3.1
10, 15	62	15000	57.4	16.1	10...24	36.6	92	5	6.1
20	62	15000	57.4	16.1	18...24	36.6	120.5	5	6.1
30	75	15000	64	18	18...28	41	121.5	6	10.4

Please specify requested bore  $\varnothing D$  at order.

