

Model T2 / T4 with single flex coupling type MWS for 0.03 to 2 Nm

nominal torque [Nm]	type MWS; size [mm]	max. speed [U/min]	dimensions [mm]							MA [Nm]
			A	B	C	D	E	F	LA	
0.03, 0.05	12	12000	82.5	17	14	4 - 6	12	2 x M2.5	72	0.5
0.1, 0.2	16	12000	107.5	29	18	4 - 8	16	2 x M3	94	0.7
0.5, 1	25	12000	116	33.5	25	5 - 12	25	2 x M4	96.5	1.7
2	32	12000	124	37.5	32	8 - 14	32	2 x M4	98.5	1.7

Please specify requested bore $\varnothing D$ at order.

