

Model T3 / T5 with double flex coupling type MST for 0.03 to 2 Nm

| nominal torque [Nm] | type MST; size [mm] | max. speed [U/min] | dimensions [mm] | | | | | | | MA [Nm] |
|---------------------|---------------------|--------------------|-----------------|------|------|--------|----|----------|-------|---------|
| | | | A | B | C | D | E | F | LA | |
| 0.03, 0.05 | 12 | 12000 | 92 | 21.5 | 18.5 | 3 - 6 | 12 | 2 x M2.5 | 82 | 0.5 |
| 0.1, 0.2 | 16 | 12000 | 118 | 34.5 | 23 | 4 - 8 | 16 | 2 x M3 | 105 | 0.7 |
| 0.5, 1 | 25 | 12000 | 130 | 40.5 | 31 | 5 - 12 | 25 | 2 x M4 | 113 | 1.7 |
| 2 | 32 | 12000 | 165.5 | 47 | 41 | 6 - 16 | 32 | 2 x M4 | 141.5 | 1.7 |

Please specify requested bore $\varnothing D$ at order.

