

Model T8 with single flex coupling type MWS for 0.2 to 2 Nm

nominal torque [Nm]	type MWS; size [mm]	max. speed [U/min]	dimensions [mm]							MA [Nm]
			A	B	C	D	E	F	LA	
0.2	16	12000	122.5	28.5	18	4 - 8	16	2 x M3	109	0.7
0.5, 1	25	12000	131	33	25	5 - 12	25	2 x M4	111.5	1.7
2	32	12000	139	37	32	8 - 14	32	2 x M4	113.5	1.7

Please specify requested bore $\varnothing D$ at order.

