

Model T8 with double flex coupling type 969 (clamping hub) for 0.2 to 20 Nm

nominal torque [Nm]	type 969; size	max. speed [U/min]	dimensions [mm]									MA [Nm]
			A	B	D	E	F	LA	P	U	S	
0.2	25	8000*	25.4	9	3...10	15	35	111.3	M4	7.8	22	1.4
0.5, 1	37	8000*	35.8	13.2	4...14	15	35	114.6	M4	9.6	27	1.4
2, 5	50	8000*	44.5	13.4	8...18	15	35	122.4	M5	11.2	3.6	3.1
10, 15	62	8000*	57.4	16.1	10...24	15	35	128.8	M5	13.8	4.4	6.1
20	62	6000*	57.4	16.1	10...24	15	35	168.8	M5	13.8	4.4	6.1

*increased number of revolutions on request

Please specify requested bore $\varnothing D$ at order.

