

Model T8 with double flex coupling type 951.3_1 for 50-200 Nm

Specifications

Typ 95...

size	max. torque TK_{max} [Nm]	max. speed N_{max} [min ⁻¹]
16	160	6000*
25	250	6000*

*increased number of revolutions on request

All elements of the coupling are machined all over and are there for in the range Q 6,3 according to VDI-characteristics 2060 with medium speed.

nominal torque [Nm]	Typ 95... size	dimensions [mm]															
		D		ds		dP		dR		dG		d1	d2	l	l1	U1	LA
50, 100	16	77	73	14	26	16	32	25	35	30	45	50	53	40	35	26.2	201.4
200	25	89	84	20	36	20	40	30	40	35	55	60	64	45	40	26.4	211.8

Please specify requested bore $\varnothing d$ at order.

