

Model T8 with single flex coupling type 950.3_0 for 50 to 200 Nm

Specifications

Typ 95...

Size	max torque TK_{max} [Nm]	max. speed N_{max} [min ⁻¹]
16	160	6000*
25	250	6000*

*increased number of revolutions on request

All elements of the coupling are machined all over and are there for in the range Q 6,3 according to VDI-characteristics 2060 with medium speed.

nominal torque [Nm]	Typ 95.. size	Dimensions [mm]															
		D		ds		dP		dR		dG		d1	d2	l	l1	s	LA
		min	max	min	max	min	max	min	max	min	max						
50	16	77	73	14	26	16	32	25	35	30	45	50	53	40	35	7.1	166.2
100	16	77	73	14	26	16	32	25	35	30	45	50	53	40	35	7.1	174.2
200	25	89	84	20	36	20	40	30	40	35	55	60	64	45	40	7.2	176.4

Please specify requested bore ϕd at order.

