


Model 9320 Hand Held Battery Powered Indicator



- TEDS Plug & Play Ready
- 7 1/2 digit bipolar LCD display
- Dual range with unit labels
- Environmentally sealed
- Peak/valley hold
- Display hold
- Gross/net
- 25 Hz update rate
- Shunt cal
- Power save mode
- mV/V Calibration



SPECIFICATIONS

ELECTRICAL

Excitation Voltage.....5 VDC
 Current.....59 mA

PERFORMANCE

Maximum Display Counts.....±9999999
 Internal Resolution24 bit
 Signal Input Range±5 mV/V
 Readings Per Secondto 25, selectable
 Nonlinearity0.005% FS

ENVIRONMENTAL

Operating Temperature.....14 to 122°F
 -10 to 50°C
 EnclosureSealed IP65/NEMA 4X
 (when mating plug fitted)

POWER

Power.....2 x AA alkaline batteries
 Battery Life45 hrs
 (450 hrs in low power mode)

MECHANICAL

Size3.5" W x 6.0" H x 1.3" D
 90 mm x 152 mm x 34 mm
 Weight0.5 lb (250 g)
 Display7 1/2 digit LCD display,
 8.8 mm digits

OPTIONS

Serial RS232 Port provides streaming ASCII for print, remote display and logging.

Carry case