



Model 9390 Battery Powered Weight Indicator

- Large 1" high contrast LCD display
- 6-digits
- 100,000 graduations
- Powers up to 4 load cells
- Battery powered
- 15 updates/second typical
- Configurable standby mode for extended battery life
- Full front-panel digital calibration & configuration
- Three-stage digital filtering
- Full Duplex RS-232



SPECIFICATIONS

ELECTRICAL

Excitation Voltage.....5 ±0.5VDC,
4 x 350Ω load cells or
8 x 700Ω load cells

PERFORMANCE

Maximum Display Counts.....100,000
Analog Signal Input Range4.5 mV/V
Sensitivity.....0.3 μV/graduation min.
Measurement Rate30, 15, 7.5, 3.75/second

ENVIRONMENTAL

Operating Temperature.....14 to 104°F
-10 to 40°C

POWER

Power.....9 VDC provided by 6 "C"
cells or included AC adaptor

MECHANICAL

Weight4.6 lb with batteries
EnclosureNEMA 4X/IP66
stainless steel
Enclosure Size9.0 in x 3 in x 5.52 in
Display6 digit LCD, 1" high

OPTIONS

Carrying case for portable use
Please specify if CE mark is required