




Edges or Dimensions DIN 6784				General Tolerances		Scale: 1:1	Weight:	Art.:
Inside Edges $\sqrt{r0.5}$				ISO 2768-mK		Semi-Finished Product: -		
Outer Edges $\sqrt{r0.3}$				Surface: DIN EN ISO 1302		Material: 3.2315 oder 3.4365		
Thread Countersinks DIN 76 Under 90_ Until 120_ Until Thread Outside Diameter				$\sqrt{Rz6,3}$		Component Naming:		
				Edit	01.11.16	Ground Platform 6A80		
				Tstd.	03.11.16			
				Std.				
				Interface, Inc.		Drawing Number:		Sheet: -
				480-948-5555		6A80-Ground-Platform-001(a)		- Leaves
				www.interfaceforce.com		Replacement for: -		Format: A
Cond.	The Change	Date	Name	Observe the protective notice DIN 34				