

GLBM Button Load Cell Specification

Dimensions

Capacity	D1 mm [in]	D2 mm [in]	H mm [in]	L mm [in]	A in	B mm [in]	G mm [in]
100 N	25,4 [1.00]	5,33 [0.21]	8.13 [0.32]	1,27 [0.05]	M3	5,59 [0.22]	19,05 [0.750]
200 N							
500 N							
1 kN	31,75 [1.25]	8,13 [0.32]	9,91 [0.39]	1,27 [0.05]	M4	6,35 [0.25]	25,4 [1.000]
2 kN							
5 kN							
10 kN							
15 kN	38,1 [1.50]	10,16 [0.40]	16,0 [0.63]	2,03 [0.08]	M4	6,35 [0.25]	31,75 [1.250]
20 kN							
50 kN							
100 kN	50.3 [1.98]	15.24[0.60]	25.4 [1.00]	3.05 [0.12]	M4	6,35 [0.25]	41.3 [1.625]
150 kN							
200 kN	75.7 [2.98]	19.8 [0.78]	38.1 [1.50]	4.6 [0.18]	M4	6.4 [0.25]	60.5 [2.375]

