


LOAD CELL CHARACTERISTICS	
CAPACITY	25K, 50K (lbf)

Interface Inc. claims proprietary rights in the information disclosed herein. This drawing is furnished in confidence on the express understanding that neither it nor any reproduction thereof will be disclosed to others or used for the purpose of manufacture or procurement of the article or part shown herein without written permission of Interface Inc. The drawing shall remain the property of Interface Inc. and shall be returned upon request by Interface Inc.

82661

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/21/2019	SKD



IDENTIFICATION LABEL INCLUDING:  
MODEL, CAPACITY & SERIAL NUMBER

3. CABLE LENGTH: 5 FT [1.5 M] (STANDARD).  
NON-STANDARD CABLE LENGTH PER  
OPTION CODE.
2. OUTPUT: 2.00 mV/V (NOMINAL)
1. ALL DIMENSIONS IN INCHES.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES [mm]	
TOLERANCES ARE:	
ANGLES	± 0° 30'
.XX	± .01 [0.25]
.XXX	± .005 [0.13]
CREATOR	DATE
DESIGNED:	
DETAILED: DAVID C.	03/19/19
WEIGHT: (APPROX) 0.38 (lbs)	⊙

**Interface** 7418 E. HELM DRIVE  
**FORCE MEASUREMENT SOLUTIONS**, SCOTTSDALE, AZ 85260 USA

TITLE:  
**OUTLINE MODEL: LOAD WASHER  
 Ø4.00 OD, 25K - 50K**

SIZE: DWG. NO:	<b>82661</b>	REV:	<b>A</b>
SCALE: 2:3		SHEET 1 OF 1	