

**Model T3 / T5 with double flex coupling type MST for 0.03 to 2 Nm**

nominal torque [Nm]	type MST; size [mm]	max. speed [U/min]	dimensions [mm]							MA [Nm]
			A	B	C	D	E	F	LA	
0.03, 0.05	12	12000	92	21.5	18.5	3 - 6	12	2 x M2.5	82	0.5
0.1, 0.2	16	12000	118	34.5	23	4 - 8	16	2 x M3	105	0.7
0.5, 1	25	12000	130	40.5	31	5 - 12	25	2 x M4	113	1.7
2	32	12000	165.5	47	41	6 - 16	32	2 x M4	141.5	1.7

Please specify requested bore  $\varnothing D$  at order.

