

Model T8 with single flex coupling type 966 for 0.2 to 20 Nm

| nominal torque [Nm] | type 966; size | max. speed [U/min] | dimensions [mm] | | | | | | | | MA [Nm] |
|---------------------|----------------|--------------------|-----------------|------|------|---------|----|----|-------|----|---------|
| | | | A | B | C | D | E | F | LA | P | |
| 0.2 | 25 | 8000* | 25.4 | 9 | 20,2 | 3...10 | 15 | 35 | 104.4 | M4 | 1.4 |
| 0.5, 1 | 37 | 8000* | 35.8 | 13.2 | 29.1 | 4...14 | 15 | 35 | 105.4 | M4 | 1.4 |
| 2, 5 | 50 | 8000* | 44.5 | 13.4 | 30.4 | 8...18 | 15 | 35 | 105 | M5 | 3.1 |
| 10, 15 | 62 | 8000* | 57.4 | 16.1 | 36.6 | 10...24 | 15 | 35 | 108.8 | M5 | 6.1 |
| 20 | 62 | 6000* | 57.4 | 16.1 | 36.6 | 10...24 | 20 | 40 | 148.8 | M5 | 6.1 |

*increased number of revolutions on request

Please specify requested bore $\varnothing D$ at order.

