

Model HRBSC High Resolution Signal Conditioning Board

- Nonlinearity <0.001% full scale
- 22-bit resolution
- High thermal stability
- Shunt calibration, software selectable
- Auto ID with Gold Standard load cells
- ISA slot plug-in board
- Bipolar

The model HRBSC is a single-channel high resolution signal conditioning board. This board offers many additional features over the SCB1 for users requiring the highest levels of accuracy and precision.


OPTIONS*

5 VDC excitation
Special shunt calibration resistors

ACCESSORIES

CT-134-10 Interconnect cable
(1600 type)
CT-141-10 Interconnect cable
(1000 type)
DA-101 Digital-Analog board,
used with automated systems
(consult factory)
GS-USB Chassis to house Signal
Conditioning Board(s)

Consult factory for more technical information



SPECIFICATIONS

EXCITATION

Excitation voltage 10VDC ±1%, mV ripple max
80-5000 ohm load

PERFORMANCE

Internal Resolution 22 bits
Signal Input Range -4.5 to +4.5 mV/V
Integration Time Software selectable from
1, 10, 16.7, 20, 100, 166.7
and 300 msec
Nonlinearity <0.001% full scale
Span Temperature Coefficient <5ppm/°C
Zero Temperature Coefficient <0.1 microvolt/°C
Span Stability—after 60 min warmup ±0.001%, 24 hrs.
±0.003%, 1 yr.
Zero Stability— after 60 min warmup ±5 microvolts, one year
Response <0.5 sec to within 0.01% basic
analog response. Response
rate equals 3 seconds for 100
msec conversion time and
standard digital filter
Input Resistance >100 megohm
Common Mode Rejection >120dB @ 60Hz,
>110 dB @ DC
Common Mode Voltage ±8 V without damage
±5 V for specified common
mode reject
Noise <0.25 µvolt typical, 0.6 µvolt
max peak with 350 ohm load,
@ 100 msec integration time
and 10 sample average

ENVIRONMENTAL

Operating Temperature 35 to 105 °F
Relative Humidity-MAX 80%
Power
DC PC BUS +5 V supply
Power Consumption 10 watts max
Mechanical
Outline 3.75 x 14 x .75 in
(95 x 356 x 19 mm)
Full size card
Connector DE-9 socket