




Position	Crowd	Art.	Designation	Drawing
1	1	8678 8679	6A110	6A110_MP11_000(b)
2	1		Ground Platform	SO062_001(a)
3	1		Adapter Plate	SO062_002(a)
4	1	-	Flange Robot	-
5	6	9084	s-DIN7984-M8x18	-
6	6	9085	s-DIN7984-M8x20	-
7	6	9086	s-DIN7984-M10x16	-
8	1	9087	s-DIN7979-D6-m6x24-St	-
9	1	9088	s-DIN7979-D8-m6x24-St	-
10	2	9100	s-DIN7979-D6-m6x16-St	-

Edges or Dimensions DIN 6784				General Tolerances		Scale: 1:2	Weight: -	Art.:
Inside Edges $\sqrt{0.2}$ Outer Edges $\sqrt{0.2}$				ISO 2768-mK		Semi-Finished Product: -		
Thread Countersinks DIN 76 Under 90_ Until 120_ Until Thread Outside Diameter				Surface: DIN EN ISO 1302		Material:		
						Component Naming:		
				Edit		20.06.17		
				Tstd.		28.06.17		
				Std.				
				Interface, Inc.		Component Naming:		
				480-948-5555		6A110-Adaptation-000(a)		
				www.interfaceforce.com		Replacement for: -		
				Observe the protective notice DIN 34				
						Sheet: -		
						Leaves		
						Format: A		