




Interface Inc. claims proprietary rights in the information disclosed herein. This drawing is furnished in confidence on the express understanding that neither it nor any reproduction thereof will be disclosed to others or used for the purpose of manufacture or procurement of the article or part shown hereon without written permission of Interface Inc. The drawing shall remain the property of Interface Inc. and shall be returned upon request by Interface Inc.

82646

REVISIONS

REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/7/2019	JAMES R.

IDENTIFICATION LABEL INCLUDING:
MODEL, CAPACITY & SERIAL NUMBER



COMPRESSION UPSCALE

		CAPACITY (lbf)				
DIM "A"	MODEL	5	10	25	50	100
0.125	2013	●	●	●	●	●
0.188	2019	●	●	●	●	●
0.250	2025	●	●	●	●	●
0.375	2038	●	●	●	●	●
0.500	2050	●	●	●	●	●
0.625	2063	●	●	●	●	●

3. CABLE LENGTH: 5 FT [1.5 M] (STANDARD).
NON-STANDARD CABLE LENGTH PER
OPTION CODE.
2. OUTPUT: 2.00 mV/V (NOMINAL)
1. ALL DIMENSIONS IN INCHES.

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES [mm]
TOLERANCES ARE:
ANGLES ± 0° 30'
.XX ± .01 [0.25]
.XXX ± .005 [0.13]

CREATOR	DATE
DESIGNED: JAMES R.	03/05/19
DETAILED: DAVID C.	03/05/19
WEIGHT: (APPROX) 0.29 (lbs)	

Interface
FORCE MEASUREMENT SOLUTIONS

7418 E. HELM DRIVE
SCOTTSDALE, AZ 85260 USA

TITLE:
**OUTLINE MODEL:
LW20XX, 5 - 100 lbf**

SIZE: DWG. NO:
A 82646

SCALE: 1:1 SHEET 1 OF 1

REV: **A**